


All dimensions are in millimeters (mm)


Alignment Key  
Front View




Recommended Panel Cut-Out



Mounting nut torque (Nm)  
Metal shell = 2.5  
Plastic shell = 0.4



Insert Configuration  
Rear View



**Note:**

1) This picture is generic and for illustrative purposes only, and may show different keying, materials, colour, finish, and contact configuration. Minor shape or feature variations to actual item may be present.

All additional information are documented on the datasheet (See below link or QR Code)  
[www.lemo.com/pdf/EEG.0B.305.CLL.pdf](http://www.lemo.com/pdf/EEG.0B.305.CLL.pdf)

Model  
EEG.0B.305.CLL

Alignment Key

Series

Insert Config.

Housing  
Insulator  
Contact  
Variant

Datasheet



**Fixed socket, nut fixing (back panel mounting)**  
Series 0B



LEMO SA  
Chemin des Champs-Courbes 28  
1024 Ecublens - SWITZERLAND

Tel. (+41 21) 695 16 00  
email : [info@lemo.com](mailto:info@lemo.com)  
[www.lemo.com](http://www.lemo.com)

CD

|                      |            |                   |
|----------------------|------------|-------------------|
| Drawn                | 06.01.2014 | OVU / JPBA        |
| Checked              | 24.04.2026 | OBAR              |
| Modified             | 01         | 24.04.2026 / JMIG |
| DO NOT SCALE DRAWING |            |                   |

**EEG.0B.305.CLL**