



Collet

: Brass (UNS C38500)

Nickel plated (SAE AMS QQ N 290)

REFERENCE	Note	ϕ Collet (mm)		ϕ Cable (mm)	
		ϕA	ϕB	max.	min.
FGG.3B.762.DN		6,2	10,2	6,2	4,9
FGG.3B.772.DN		7,7	10,2	7,7	6,3
FGG.3B.792.DN		9,2	10,2	9,2	7,8
FGG.3B.710.DN		10,0	10,2	10,0	9,3
FGG.3B.711.DN		11,0	10,2	11,0	10,1
FGG.3B.712.DN	1) 2)	12,0	10,2	12,0	11,1

Note : 1) Can not be used with collet nut for bend relief .

Note : 2) Collet nut to use : FGG.3B.132.LC

Collet . (New design)
Series 3B

ETUDE N° E6040-E7195

Echelle —	Dessiné	23.04.2008	OVU / RMO
	Contrôle	15.12.2020	NHA / CDE
	Modif.	05	15.12.2020/ OVU



LEMO

LEMO SA
Chemin des Champs-Courbes 28
1024 Ecublens - SWITZERLAND

Tel. (+41 21) 695 16 00
email : info@lemo.com
www.lemo.com

FGG.3B.7___.DN