







Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Clip	: Cu-Be (UNS C17200)	-
Notched nut	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Contact wire	: Bronze (UNS C27400)	Tinned
Position insert	: FEP	-

Panel cut-out



Torque for mounting
nut : 4.5 Nm

A-A cross-section (PCB drilling pattern)



Spanner for notched nut : DCH.91.161.PA

Fixed socket , with two nuts , with key (G) , with elbow (90°) contact for PCB . (Back panel mounting) .
Series 1B , multipole (4)

ETUDE N°

Echelle

Dessiné

16.06.03

OVU / RMO

Contrôle

16.06.03

RMO / CDE

Modif.

00

16.06.03 / OVU



LEMO

CH-1024 Ecublens

ECG.1B.304.CLV