





Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Clip	: Cu-Be (UNS C17200)	-
Notched nut	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Contact wire	: Bronze (UNS C27400)	Tinned
Position insert	: POM	-



Spanner for notched nut : DCH.91.121.PA

Fixed socket , with two nuts , with key (G) , with elbow (90°) contact for PCB . (Back panel mounting) .
Series 0B , multipole (3)

ETUDE N° E6158

Echelle

Dessiné

31.03.88

MRI / RMO

Contrôle

22.06.01

RMO / CDE

Modif.	
--------	--

04

22.06.01 / OVU



CH-1024 Ecublens

ECG.0B.303.CL V