







Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Notched nut	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)

Panel cut-out



Torque for
mounting
nut : 2.5 Nm

PCB drilling pattern



Spanner for notched nut : DCH.91.121.PA

Fixed socket , with two nuts , with key (G) ,
for PCB . (Back panel mounting) .
Series 0B , multipole (6)

ETUDE N°

Echelle

Dessiné

16.03.98

RM0 / RM0

Contrôle

09.04.02

RM0 / CDE

Modif.

01

09.04.02 / OVU



LEMO

CH-1024 Ecublens

ECG.0B.306.CLN