





Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Clip	: Cu-Be (UNS C17200)	-
Notched nut	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic part	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Contact wire	: Bronze (UNS C27400)	Tinned
Position insert	: FEP	-

Figure 1: Schematic diagram of the test specimen. The diagram shows a vertical assembly with four points labeled 1, 2, 3, and 4. Points 1 and 2 are at the bottom, 3 and 4 are at the top. The vertical distance between the top and bottom points is 2.54. A horizontal dimension line at the top indicates a width of $0.7^{+0.1}_{-0} (\times 4)$.



LEMP SA

CH-1024 Ecublens

EEG.1B.304.CL V