







Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Notched nut	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Contact wire	: Bronze (UNS C27400)	Tinned
Position insert	: FEP	-

Panel cut-out



Torque for
mounting
nut : 2.5 Nm

A-A cross-section (PCB drilling pattern)



Spanner for notched nut : DCH.91.121.PA

Fixed socket , with two nuts , with key (G) , with
elbow (90°) contact for PCB . (Back panel mounting) .
Series 0B , multipole (9)

ETUDE N° E6312

Echelle

Dessiné

24.01.03

FBO / RMO

Contrôle

08.04.03

CDE / CDE

Modif.

02

07.02.03 / FBO



LEMO

CH-1024 Ecublens

ECG.0B.309.CLV