






Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Insulator	: PTFE	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)

Panel cut-out



Torque for
mounting
nut : 4.5 Nm

Spanner for nut : DCA.91.201.4TN or
Spanner for nut : DCG.91.201.4TN

Fixed socket , with nut fixing .
Series 1S , coaxial (50 Ω)

ETUDE N° E7067

Echelle

—

Dessiné	09.09.04	OVU / RMO
Contrôle	09.09.04	RMO / CDE
Modif.	00	09.09.04 / OVU



LEMO SA

CH-1024 Ecublens

ERA.1S.250.CTL