






|                      |                       |                              |
|----------------------|-----------------------|------------------------------|
| Outer shell          | : Brass (UNS C38500)  | Chrome plated (FS-QQ-C-320B) |
| Earthing crown       | : Bronze (UNS C54400) | Gold plated (ISO 4523)       |
| Insulator            | : PTFE                | -                            |
| Female contact       | : Bronze (UNS C54400) | Gold plated (ISO 4523)       |
| Locking washer       | : Bronze (UNS C52100) | Nickel plated (FS-QQ-N-290A) |
| Other metallic parts | : Brass (UNS C38500)  | Nickel plated (FS-QQ-N-290A) |

Panel cut-out



Torque for  
mounting  
nut : 4.5 Nm

Spanner for nut : DCA.91.201.4TN or  
Spanner for nut : DCG.91.201.4TN

**Fixed socket , with nut fixing .**  
**Series 1S , coaxial (50Ω)**

ETUDE N° E2446

Echelle

—

|          |          |                |
|----------|----------|----------------|
| Dessiné  | 08.12.09 | OVU /JPBA      |
| Contrôle | 08.12.09 | JPBA / CDE     |
| Modif.   | 00       | 08.12.09 / OVU |



**LEMO** 

CH-1024 Ecublens

**ERP.1S.250.CTL**