



Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Latch sleeve	: Special brass	Nickel plated (FS-QQ-N-290A)
Female sleeve	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Collet nut	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Insulators	: PTFE	-
Male contact	: Brass (UNS C38500)	Gold plated (ISO 4523)
Retaining ring	: Brass (UNS C38500)	Gold plated (ISO 4523)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)

Assembly instruction per customer drawing : FFA.0S.652.CTAC44

Straight plug , with cable collet , solder contact with inner screen to solder into the retaining ring with internal hole $\phi 1.4$
Series 0S , triaxial (50Ω) (without collet)

ETUDE N° E2080

Echelle —	Dessiné	02.11.2011	OVU / JPBA
	Contrôle	02.11.2011	JPBA / ATVI
	Modif.	00	02.11.2011 / OVU



LEMO

CH-1024 Ecublens

FFA.0S.652.CTAZ