


Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Latch sleeve	: Special brass	Chrome plated (FS-QQ-C-320B)
Inner shell	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Nut + collet nut + clamp	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Insulator + insulating sleeve	: PTFE	-
Insulating sleeve + collet	: PEEK	-
Male contact	: Brass (UNS C38500)	Gold plated (ISO 4523)
Male sleeve	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Clips	: Bronze (UNS C54400) + Cu-Be (UNS C17300)	Nickel plated (FS-QQ-N-290A)
Gland	: Silicone (SI)	-
Other earthing pieces	: Brass (UNS C38500)	Gold plated (ISO 4523)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Screw	: Stainless steel	-



Câble recommandés : Acome , Filotex Type A BELDEN 9267 BICC T 1892 - T 1893 FMC Triax 8 CABELTEL Triax A2 UR	Flat spanners set : DCP.91.023.TN Assembly plier : DCF.91.023.TA
--	---

**Straight plug , with cable collet with clamp .
(For solder of the external screen) .
Série 3T , triaxial (75Ω)**

ETUDE N° E2071-E1814C-E1715

Echelle	Dessiné	21.04.94	XK0 / RMO
	Contrôle	22.10.09	JPBA/ CDE
	Modif.	01	22.10.09 / OVU