





Outer shell	: Brass (UNS C38500)	Chrome plated (SAE AMS 2460)
Earthing crown	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Conical nut	: Brass (UNS C38500)	Chrome plated (SAE AMS 2460)
Ground pin	: Stainless steel (AISI303)	Gold plated (ISO 27874)
Sealing resin	: Epoxy	-
O-rings	: Silicone (MVQ)	-



PCB drilling pattern



Spanner for conical nut : DCM.65.000.4PA
Insert for conical nut : DCM.65.200.AZ

ETUDE N° E11362-E10742-E6363-E6342-E1678-E6362

Dessiné	09.12.2020	OVU / NHA
---------	------------	-----------

Modif.	00	09.12.2020/ OVU
--------	----	-----------------

**LENO**

Tel. (+41 21) 695 16 00
email : info@lemo.com
www.lemo.com

HEP.3M.330.CLNP