


Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Brass (UNS C38500)	Gold plated (ISO 4523)
Nut + collet nut + clamp	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Insulator + insulating sleeve	: PTFE	-
Insulating sleeve + ring	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Female sleeve	: Brass (UNS C38500)	Gold plated (ISO 4523)
Clip	: Cu-Be (UNS C17300)	Nickel plated (FS-QQ-N-290A)
Glands	: Silicone (SI)	-
Other earthing pieces	: Brass (UNS C38500)	Gold plated (ISO 4523)
Screw	: Stainless steel	-



Cable recommended : FMC Triax 11

**Straight socket , with cable collet with clamp .
(For solder of the external screen) .
Série 3T , triaxial (75Ω)**

ETUDE N° E1814-E1918-E1715

Echelle	Dessiné	28.01.2014	OVU / JPBA
	Contrôle	28.01.2014	JPBA / ATVI
	Modif.	00	28.01.2014 / OVU